




NOTE:

CURTAIN CANNOT OCCUPY SPACE BETWEEN THE TWO (2) MODEL 2803 LIVE END PULLEYS. THIS AREA MUST REMAIN CLEAR TO ALLOW FOR MOVEMENT OF SANDBAG.

MINIMUM DISTANCE BETWEEN THE 2 MODEL 2803 LIVE END PULLEYS IS 3'

SANDBAG SHOULD ONLY BE FILLED WITH ENOUGH SAND TO PROVIDE NECESSARY TENSION TO THE CABLE.

CURTAIN MACHINE SHOULD BE EQUIPPED WITH OPTIONAL CTD-1 CABLE TENSION DEVICE.

AUTOMATIC DEVICES COMPANY				
2121 S. 12TH ST. ALLENTOWN, PA 18103				
THIS DRAWING HAS BEEN PREPARED AS A SERVICE TO OUR CUSTOMER AND IS INTENDED ONLY TO BE SUGGESTIVE IN NATURE AND IS NOT TO BE USED AS AN ACTUAL INSTALLATION DRAWING. PREVAILING JOB CONDITIONS AND ACCEPTED PRACTICES MUST BE TAKEN INTO ACCOUNT WHEN THE EQUIPMENT IS INSTALLED.				
SIZE	DATE	SANDBAG TENSION		REV
A	08/22/10	DEVICE		
DRAWN BY	APPROVED BY	DESCRIPTION		
DJL		MODEL 280 SBTD		
SCALE	NTS	SHEET	OF	DWG NO. A-280SBTD-10